

# ReproCut™

Cutting Edge Solutions

## New Specially Designed Tool Safely and Easily Cuts all Flexbar Reprorubber® Castings



- 2.25" Throat clearance, 2.5" Cutting Blade Width
- Easily trim flash and excess material
- Two sided operation
  - Single blade for variable thickness slicing
  - Dual blade for repeatable putty specimens
- Two handed operation improves accuracy & avoids injury
- Clear window allows direct view of cutting area
- Safety Cover doubles as a specimen removal tool

**Model No. 16139** - ReproCut™ Cutting Tool System

*Replacement Blades:*

**Model No. 16139-SB**, Replacement Thin Cutter Blade

**Model No. 16139-LB**, Replacement Thick Cutter Blade



Unique Products • Innovative Solutions

### NEW FROM FLEXBAR

Reprocut is the perfect compliment to our popular Reprorubber® product line.

### IMPROVES ACCURACY

Produces even and accurate cross-sections of specimens that can be easily inspected.

### AVOIDS WORKPLACE INJURY

Two handed operation keeps user out of harms way.

### INDUSTRIAL APPLICATIONS

Metalworking

Automotive

Aerospace

Oil & Gas

Medical Devices

Plastics

Sheet Metal & Stampings

Forensics

Art Restorations



Many More

# Flexbar ReproCut™



## Uses & Applications

*Produces Sharp and Accurate Cross-Sectioned Replicas for use with Optical Comparators & Video Measurement*

### Radius Measurements



### Length/Angle Measurements



### Pitch Diameter



### REPRORUBBER SUPPLIED IN THREE VISCOSITIES:

#### ORIGINAL THIN POUR

For internal-shape applications where a thin pour will completely fill the cavity without voids.

#### MEDIUM BODY - ORANGE

Medium body casting material ideal for both internal and external applications. Disposable prefilled dual barrel 50ml cartridges can quickly dispense casting material utilizing the REPRO-MIX II Gun System.

#### QUICK SETTING PUTTY

Roll two equal-sized balls of catalyst putty and base putty and simply knead them together like dough. Excellent for external shapes.

For more information on any of our products or services please visit us on the Web at:

[www.repro-rubber.com](http://www.repro-rubber.com)

#### QUICK SETTING PUTTY



Safety Cover doubles as a specimen removal tool

#### ORIGINAL THIN POUR



#### MEDIUM BODY - ORANGE



FLEXBAR MACHINE CORPORATION  
250 Gibbs Road • Islandia, NY 11749  
Phone 631.582.8440  
Fax 631.582.8487  
Toll-free 800.879.7575  
[www.flexbar.com](http://www.flexbar.com)

© 2016 Flexbar Machine Corp., Islandia, NY USA